

Within Series Adaptor 32_MMBX-50-0-1/111_N

Description

Adaptor plug/plug
MMBX plug (male) / MMBX plug (male)

Slide - snap interface

Interface standard
Series MMBX - SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	12.4 GHz		
Frequency range	DC to 2 GHz	2 to 6 GHz	6 to 8 GHz
Return loss	≥ 26 dB	≥ 25 dB	≥ 16 dB

Mechanical Data

Number of matings	100
Weight	0.0001 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Interface - MMBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013781
-----------------	--------------

Ordering Information

Single package	32_MMBX-50-0-1/111_NE
Tray package	32_MMBX-50-0-1/111_NY