

Coaxial PCB Connector 85_SMB-Z50-0-19/111_N

Description

Right angle PCB jack

Interface Standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0021 kg

Environmental Data

Operating temperature -40 °C to 100 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Zinc Alloy	SUCOPRO Plating
Body	Zinc Alloy	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00013184
Catalogue drawing DCA-00013186

Ordering Information

Bulk 100 pcs package 85_SMB-Z50-0-19/111_NH
Single package 85_SMB-Z50-0-19/111_NE

Remarks

PCB connector with stand-offs