

## Coaxial Cable Connector 21\_UHF-0-7-4/033\_

### Description

Straight cable jack

Interface standards

IEC 60169-12



### Technical Data

#### Electrical Data

Impedance other  $\Omega$   
Interface frequency max. 0.2 GHz

#### Mechanical Data

Centre contact crimped  
Outer contact crimped  
Weight 0.0324 kg

#### Environmental Data

Operating temperature -55 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing DOU-00007985  
Catalogue drawing DCA-00006309  
Assembly instruction DOC-0000201061

### Ordering Information

Single package 21\_UHF-0-7-4/033\_E

### Additional Information

Suitable cables RG\_213\_/U, GX\_07272, G\_07262, G\_07272, RADOX\_RF\_213