

## Coaxial Panel Connector 13\_BMA-50-0-2/199\_N

### Description

Straight panel receptacle plug, flange mount

Interface standards

IEC 60169-33\_MIL-STD-348A/321



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Number of matings	1000
Weight	0.0025 kg

#### Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

### Related Documents

Catalogue drawing	DCA-00011086
-------------------	--------------

### Ordering Information

Single package	13_BMA-50-0-2/199_NE
----------------	----------------------