

Coaxial PCB Connector 86_CT-0-1-1/111_N

Description

Right angle PCB cable terminator

Interface Standards



Technical Data

Electrical Data

Impedance other Ω

Mechanical Data

Board mounting type through holes
Weight 0.0003 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012736
Catalogue drawing DCA-00012738
Assembly instruction DOC-0000192830
Mounting hole DOU-00012739

Ordering Information

Bulk 100 pcs package 86_CT-0-1-1/111_NH
Single package 86_CT-0-1-1/111_NE

Remarks

PCB connector without stand-offs, suitable for cable group U1(RG_178_B/U), cable entry: soldered