

Coaxial Cable Connector 11_MCX-75-2-1/113_N

Description

Straight cable plug

Interface standards
SUHNER-MCX75



Technical Data

Electrical Data

Impedance	75 Ω		
Interface frequency max.	6 GHz		
Frequency range	DC to 1 GHz	1 to 2.5 GHz	2.5 to 6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0021 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DOU-00006170
Assembly instruction	DOC-0000179381

Ordering Information

Bulk 100 pcs package	11_MCX-75-2-1/113_NH
Single package	11_MCX-75-2-1/113_NE

Additional Information

Suitable cables	RG_179_B/U, RG_187_A/U, RG_187_A/U
-----------------	------------------------------------