

Coaxial Panel Connector 23_SMA-50-0-61/199_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Number of matings	500
Weight	0.0018 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00010361
-------------------	--------------

Ordering Information

Single package	23_SMA-50-0-61/199_NE
----------------	-----------------------