

Coaxial Cable Connector 21_MM CX-50-1-2/111_O

Description

Straight cable jack

Interface standards

SUHNER-MM CX

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0008 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

Related Documents

Catalogue drawing DOU-00005909
Assembly instruction DOC-0000179110

Ordering Information

Single package 21_MM CX-50-1-2/111_OE

Additional Information

Suitable cables K_01152-07