

Coaxial PCB Connector 82_MMCX-S50-0-55/119_O

Description

Straight PCB jack

Interface Standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	surface mount
Weight	0.0002 kg

Environmental Data

Operating temperature	-40 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating
Outer contact	Brass	Gold Plating
Body	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00080629
Mounting hole	DOU-00012840

Ordering Information

Tape and Reel package	82_MMCX-S50-0-55/119_OM
-----------------------	-------------------------