

Coaxial Cable Connector 16_MM CX-50-1-1/111_O

Description

Right angle cable plug

Interface standards
SUHNER-MM CX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0007 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00006008
Catalogue drawing	DOU-00006007
Assembly instruction	DOC-0000779355

Ordering Information

Single package	16_MM CX-50-1-1/111_OE
Bulk 100 pcs package	16_MM CX-50-1-1/111_OH

Additional Information

Suitable cables	RG_178_B/U, RG_196_A/U
-----------------	------------------------