# **Data Sheet**



# Coaxial Panel Connector 23\_SMA-50-0-53/199\_N

### **Description**

Straight panel receptacle jack, flange mount

Interface standards
IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



#### **Technical Data**

**Electrical Data** 

Impedance 50  $\Omega$  Interface frequency max. 18 GHz

**Mechanical Data** 

Number of matings 500
Weight 0.0031 kg

**Environmental Data** 

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

#### **Material Data**

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

#### **Related Documents**

Catalogue drawing DCA-00011155

## **Ordering Information**

 Single package
 23\_SMA-50-0-53/199\_NE

 Bulk 100 pcs package
 23\_SMA-50-0-53/199\_NH