

# NYS352

Heavy duty phono plug, cable clamp



## Article Variations

Article Name	Details	Packaging
NYS352	Nickel plated shell and contacts	
NYS352AG	Gold plated shell and contacts	
NYS352B	Black plated shell, nickel plated contacts	
NYS352BG	Black plated shell, gold plated contacts	
NYS352G	Nickel plated shell, gold plated contacts	

## Technical Information

### Product

<b>Title</b>	NYS352
<b>Connection Type</b>	Plug

### Electrical

<b>Contact resistance</b>	$\leq 10\text{m}\Omega$
<b>Insulation resistance</b>	$\geq 2,000\text{M}\Omega$
<b>Dielectric strength</b>	50Hz 0.5KVdc

### Mechanical

<b>Insertion and Withdrawal force</b>	5-20N
<b>Lifetime</b>	>5,000 mating cycles

### Material

<b>Pin</b>	Brass
<b>Housing</b>	Brass
<b>Housing</b>	Zinc
<b>Insulation</b>	PP
<b>Cable Clamp</b>	Steel
<b>Pin</b>	Tin and Cer
<b>Cable Clamp</b>	Tin and Cer
<b>Housing</b>	Nickel Plating
<b>Housing</b>	Nickel Plating