



Quality Products. Service Excellence.

Type 3R Painted Galvanized Steel Enclosure *C3R HCL0 Series*

Lift-Off Hinge Door with Snap Latch



Application

- Designed for use as a wiring/junction box.
- Provides protection against rain, sleet, snow and dripping water.

Standards

- UL-50 Type 3R
- CSA Type 3R
- Complies with
 - NEMA Type 3R
 - IEC 60529, IP24

Construction

- Formed and spot welded from 16 gauge galvanized steel (14 gauge when 24" wide)
- Extended height door and seam-free sides, front and back.
- Galvanized steel lift-off hinges with stainless steel pins.
- Cover fastened securely with zinc plated draw pull catches.
- Provisions for padlocking on zinc-plated draw pull catch.
- Embossed mounting holes on back.
- Foam gasket seal around door opening.

Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

Accessories

- Additional Inner Panels
- Swing Panel Kit
- Additional Inner Panels

Part No.	Enclosure			Optional Inner Panel			Optional Panel	Optional Mount
	H	W	D	Part No.	H	W	Mounting Kit	Foot Kit
C3R864HCL0	8.00	6.00	4.00	14R0505	4.88	4.88	C3RHCL0PK1	C3RHCL0MFK1
C3R886HCL0	8.00	8.00	6.00	14R0705	6.75	4.88	C3RHCL0PK1	C3RHCL0MFK1
C3R1086HCL0	10.00	8.00	6.00	14R0707	6.75	6.88	C3RHCL0PK1	C3RHCL0MFK1
C3R12106HCL0	12.00	10.00	6.00	14R0909	8.75	8.88	C3RHCL0PK1	C3RHCL0MFK1
C3R12126HCL0	12.00	12.00	6.00	14R1109	10.75	8.88	C3RHCL0PK1	C3RHCL0MFK1
C3R16126HCL0	16.00	12.00	6.00	14R1311	12.75	10.88	C3RHCL0PK1	C3RHCL0MFK1
C3R16166HCL0	16.00	16.00	6.00	18P1313	13.00	13.00	C3RHCL0PK2	C3RHCL0MFK2
C3R20166HCL0	20.00	16.00	6.00	18P1713	17.00	13.00	C3RHCL0PK2	C3RHCL0MFK2
C3R20208HCL0	20.00	20.00	8.00	18P1717	17.00	17.00	C3RHCL0PK2	C3RHCL0MFK2
C3R24208HCL0	24.00	20.00	8.00	18P2117	21.00	17.00	C3RHCL0PK2	C3RHCL0MFK2
C3R24248HCL0	24.00	24.00	8.00	18P2121	21.00	21.00	C3RHCL0PK2	C3RHCL0MFK2
C3R30248HCL0	30.00	24.00	8.00	18P2721	27.00	21.00	C3RHCL0PK2	C3RHCL0MFK2

Data subject to change without notice

© 2022. Hammond Manufacturing Ltd. All rights reserved.