


PIN OUT



NOTES:

1. Open/Short/Intermittence: 100% Testing
2. HI-POT:AC 150V 0.01S
3. Insulation Resistance: DC200V 0.01S 10MΩ Min
4. Conductive Resistance: 5Ω Max
5. Resolution Ratio: 8K*4K@60Hz
6. RoHS & REACH COMPLIANT
7. Marking:Ultra High Speed HDMI™ Cable with Ethernet
E***** 兄 AWM STYLE 20276 80° C 30V VW-1

⑧	SCREW	Philips Screw #4-40 UNC Nickel Plated L=12mm	2	PCS
⑦	NUT	Embedded Nut #4-40 UNC Nickel Plated L=10mm	2	PCS
⑥	MOLDED	45P Black PVC		G
⑤	MOLDED	LDPE		G
④	Copper Foil	Copper Foil Tape Double Side Conductive 25*100mm	1	PCS
③	SHEATH	HDMI2.1 Female Connector Sheath Black ABS L=11mm	1	PCS
②	CONNECTOR	HDMI2.1 Female Connector Contact Pin G/F And Shell Golden Plated	2	PCS
①	CABLE	[2C*(1/0. 32BC)+D(1/0. 254TC)+AL+BOPPTape]*4+[1P*(1/0. 32BC)+D(1/0. 25BC)+AL/MYLAR]+4C*(1/0. 32BC)+MAD(1/0. 32TC)+B(16/10/0. 12 AL-MG)BLACK PVC JACKET OD:6.5±0.2mm	250	MM
NO.	MATERIAL	DESCRIPTION	QTY.	UNIT

Ltemref	Quantity	Title/Name, designation, material, dimension etc	Article NO./Reference		
Designed by	Checkde by	Approved by - date	File name	Date	Scale
ANGLE:		HDMI A F/F 2.1V Panel mount			
UNIT:MM			PRO-SIGNAL		
			Edition	Sheet	
			1	1/1	