

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0464369323](#)  
**Status:** **Active**  
**Overview:** [EXTreme Ten60 High-Power Connectors](#)  
**Description:** EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 3 DC Power Circuits, 15 Signal Circuits, 3 DC Power Circuits, Press Fit Tail

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 464361001-PK-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 464361000-TS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-46436-100-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

UL E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">46436</a>
Application	Board-to-Board, Power, Signal
Comments	See Product Specification for details
Component Type	PCB Receptacle
Overview	<a href="#">EXTreme Ten60 High-Power Connectors</a>
Product Name	EXTreme Ten60Power
Taxonomy	Board-to-Board Connectors
UPC	195842670907

**Physical**

(p)ower-(s)ignal Configuration	3p - 15s - 3p
Circuits (Loaded)	21
Circuits (maximum)	21
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	23.798/g
Number of Rows	1, 5
Orientation	Right Angle
PC Tail Length	2.50mm, 3.28mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm, 5.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[46436 Series](#)

**Mates With**

[EXTreme Ten60Power Right-Angle Plug  
464379323](#)

Temperature Range - Operating -40° to +105°C  
Termination Interface: Style Through Hole - Compliant Pin

**Electrical**

Current - Maximum per Contact 60.0A  
Grounding to PCB No  
Voltage - Maximum 600V AC / 250V DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification 464361001-PK-000  
Product Specification PS-46436-100-001  
Sales Drawing 464369330-000  
Test Summary 464361000-TS-000

This document was generated on 01/05/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**