

Technical Specification

Product Code: QOE3052BLK

Description: 5 Pole 2 Way 24A IP68 Inline Connector



Dimensions

Length (mm)	112
Minimum Cable Diameter (mm)	6
Maximum Cable Diameter (mm)	14
Diameter (mm)	30

General Information

Colour	Black (RAL 9017) & Red (RAL 3020)
Maximum Voltage (V)	450
Maximum Current Rating (A)	24
Tightening Torque (Nm)	3.8
Ingress Protection	IP68
Temperature Rating (°C)	-40 to +105
Working Temperature (°C)	100

Materials

Body Components: Nylon (PA66)
Seals: Silica Gel

Additional Information

2 x PG16 inline entries with seals.
Supplied with 5 pole connections using screw terminals.

Standards

BS 6220
BS EN 60670
BS EN 60529:1992+A2:2013 (Sections 13 & 14)