

## Technical Specification

Product Code: QOE3053BLK

Description: 5 Pole 3 Way 24A IP68 T-Connector



### Dimensions

Length (mm)	106
Width (mm)	98
Minimum Cable Diameter (mm)	6
Maximum Cable Diameter (mm)	14
Diameter (mm)	30

### General Information

Colour	Black (RAL 9017) & Red (RAL 3020)
Maximum Voltage (V)	450
Maximum Current Rating (A)	24
Tightening Torque (Nm)	3.8
Ingress Protection	IP68
Temperature Rating (°C)	-40 to +105
Working Temperature (°C)	100

### Materials

Body Components: Nylon (PA66)  
Seals: Silica Gel

### Additional Information

3 x PG16 entries with seals.  
Supplied with 5 pole connections using screw terminals.

### Standards

BS 6220  
BS EN 60670  
BS EN 60529:1992+A2:2013 (Sections 13 & 14)