


SMA Female Non-Magnetic Bulkhead Connector for .047 Cable

P/N: 2921-40054

Not available for this part number. Please contact us.



DOWNLOADS



Datasheet



C/A Instr.



CAD Model

SPECIFICATIONS

CONTACT US

RF Series

SMA

Gender

Jack (Female)

Orientation (Body)

Straight

Coupling	Threaded
----------	----------

Body Style	Jamnut/Bulkhead
------------	-----------------

Mounting Type	Panel
---------------	-------

Number of Ports	Single
-----------------	--------

Finish	Gold
--------	------

Termination Style	Solder
-------------------	--------

Cable Type	0.047 Flexible Coax
------------	---------------------

Family	Non-Magnetic
--------	--------------

Cable Builder Attributes

Mating Connector	2906-6002, 2911-40023
------------------	-----------------------

Electrical

Impedance	50 ohms
-----------	---------

Frequency	18 GHz
-----------	--------

Shielding Effectiveness	≥ -90 dB
-------------------------	----------

Dielectric withstanding Voltage	1000 VRMS
---------------------------------	-----------

Mechanical

Mating Cycles	500
---------------	-----

Mating Torque	7 - 10 in - lbs
---------------	-----------------

Inter-mate ability	2.92mm
--------------------	--------

Environmental

Temperature Rating	-65°C to +165°C
Shock	MIL-STD-202, Method 213, Condition I
Corrosion (salt spray)	MIL-STD-202, Method 101, Condition B
Vibration	MIL-STD-202, Method 204, Condition D
Thermal Shock	MIL-STD-202, Method 107, Condition B
Barometric Pressure (Altitude)	MIL-STD-202, Method 105, Condition C, 70k Ft.
Moisture Resistance	MIL-STD-202, Method 106, Less Step 7B

CUSTOMERS ALSO VIEWED

