

5-2384030-3 ✓ ACTIVE




TE Internal #: 5-2384030-3

PCI & PCI Express Connectors, Board-to-Board, 98 Position, .04 in [1 mm] Centerline, Vertical, Black, Height 11.25 mm [.44 in], Width 8.2 mm [.32 in]

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**

Number of Positions: **98**

PCI Generation: **5**

Centerline (Pitch): **1 mm [.04 in]**

Termination Post & Tail Length: **1.1 mm [.043 in]**

## Features

### Product Type Features

Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Positions	98
PCB Mount Orientation	Vertical
Ejector	Without

### Contact Features

Contact Thickness	30 $\mu$ m
Contact Current Rating (Max)	1.1 A

### Termination Features

Termination Method to Printed Circuit Board	Surface Mount
Termination Post & Tail Length	1.1 mm [.043 in]

### Mechanical Attachment



PCB Mount Retention Type	Tab
--------------------------	-----

Connector Mounting Type	Board Mount
-------------------------	-------------

### Housing Features

Centerline (Pitch)	1 mm [.04 in]
--------------------	---------------

Housing Color	Black
---------------	-------

### Dimensions

Connector Height	11.25 mm [.44 in]
------------------	-------------------

Connector Width	8.2 mm [.32 in]
-----------------	-----------------

### Usage Conditions

Operating Temperature Range	-40 – 85 °C [-40 – 185 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	High Speed Data
---------------------	-----------------

### Industry Standards

PCI Generation	5
----------------	---

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 4-2364427-4  
PCI5 GEN5 CON,SMT,164P,15u Au,S-MYLAR,HT

## Customers Also Bought



TE Part #3-5353515-0  
ON TAPING (EMBOSS) 0.5MM FS CONN. TAB AS



TE Part #3-6600333-4  
MBXL VERT HDR 4P+8S+4P

TE Part #5-6450830-0  
MBXL R/A HDR 2LP+8S+3LP

TE Part #1-2204808-8  
ELCON MICRO,HEADER,R/A DIP W /BOSS,4P

TE Part #2-2204808-8  
ELCON MICRO,HEADER,R/A DIP W /BOSS,6P

TE Part #2170460-8  
SFP+ assy 2x2 Spring Fingers No Lp Sn

TE Part #2170660-3  
XFP Networking Kit(cage, clip, heatsink)



TE Part #2187282-1  
SW PIR RECT, 100OHM, 4X4

TE Part #2204808-8  
ELCON MICRO,HEADER,R/A DIP W /BOSS,2P

TE Part #2332485-1  
RA REC ASSY 4X4, 92OHM PIR WHISPER R

## Documents

### Product Drawings

PCI5,SMT,1.9TAB+C-POS,98P,30",10 ML,HT

English



---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_5-2384030-3\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-2384030-3\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-2384030-3\\_A.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Application Specification](#)

English