



Designed to blow or suck pull line through 3/4" - 2" (18-50 mm) conduit for cable pulling, this pull line blower is perfect for running wire or cable through conduits multiple times a day. With its unique design, it makes short work of bends and kinks in conduit, saving a huge amount of time compared to mule tape or jet line. This pull line blower also features the following:

- Blows or sucks pull line without the need for a compressor
- For all commercial and residential pipe work with internal diameters from 3/4" - 2" (18 mm - 50 mm)
- Lightweight and ergonomic for superior accessibility, even in confined spaces
- Works great on flexible conduit
- Saves a tremendous amount of time compared to mule tape or jet line

Kit Includes:

- (1) PLB-1000 Pull Line Blower (aka Stringing Gun)
- (2) Pull line rolls (Ø 1 mm, tensile strength approx. 24 kg, length approx. 900 m)
- (1) Suction device
- (1) Components set A: 2 joints 1/2" reducer 19/12 mm plus nozzle int. Ø 9,5 mm
- (1) Components set B: 3 joints 3/4" nozzle int. Ø 16 mm plus nozzle int. Ø 19 mm
- (1) Special nozzle black, for int. Ø from 25 to 50 mm
- (1) Special nozzle with 90° angle, Ø ext. 12 mm
- (3) Beads (round) of Ø 11mm
- (3) Beads (round) of Ø 13mm
- (3) Beads (round) of Ø 16mm
- (1) Operating Manual

SPECIFICATIONS	
AIR FLOW	2.35 ft <sup>3</sup> /min (4 m <sup>3</sup> /h)
WEIGHT	8.8 lbs (4000 g)
UPC #	810053352137

