

AI-T00212

(Receptacle, M12 Rear Mount, 12-Position Female Straight-Open, PG9 Threads, 24 AWG, 0.5M)



• Mueller's AI-T00212 is a cable assembly that has a 12-position rear mount M12 Female receptacle to open end, 24 AWG, 0.5 meters.

M12 (A Coding)

- Shell size for connector:
- Cable Material: 24AWG Hook Up Wire
 - Overall length = 1.64' (0.5M)
- Shell: 18x18mm PG9 threaded rear mount
 - Material: Nickel Plated Brass
- Rating:

 Voltage: 	30V AC/DC
------------------------------	-----------

- Current: 1.5 Amps
- Ambient Temperature: -40°C to 85°C
- Standard: IEC 61076-2-101
- Waterproof:
- RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

IP67/IP68

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524