




[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
 Die Sets Type: **Removable/Interchangeable**
 Specification Type: **TE Product Specification (114-)**
 TE Certification: **Cannot be Certified**
 Tooling Type: **SDE Crimp Die Set**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Tooling Type	SDE Crimp Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2021 (211)



Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET

TE Part # 2063561-1
SDE P&S ROUND 12-14AWG ASSY

TE Part # 962999-1
1,5MMD SOCKET CONTACT

TE Part # 1-962972-0
2,5MM STIFTKONT EDS

TE Part # 1-962982-0
2,5MM EDS BU-KONT

TE Part # 1-962999-0
1,5MM SOCKET CONTACT LOOSE PIECE

TE Part # 1962982-2
PLUG,PROTECTIVE,TAPERED, FLANGED









TE Part # 2362810-1
SDE CRIMP HAND TOOL FRAME W /O DIES

TE Part # 962972-2
STIFTKONTAKT 2,5MMD











TE Part # 962972-7
2,5MM STIFTKONT EDS

TE Part # 962972-8
2,5MM PIN CONTACT LP (>1,0-2,5) SWS

TE Part # 962972-9
2,5MM STIFTKONT EDS

 <p>TE Part # 962982-2 BU-KONTAKT 2,5MMD</p>	 <p>TE Part # 962982-7 2,5MM EDS BU-KONT</p>	 <p>TE Part # 962982-8 2,5MM SOCKET CONTACT LP(>1,0-2,5)SWS</p>	 <p>TE Part # 962982-9 2,5MM EDS BU-KONT</p>
 <p>TE Part # 962993-2 STIFTKONTAKT 1,5MMD</p>	 <p>TE Part # 962993-3 STIFTKONTAKT 1,5MMD</p>	 <p>TE Part # 962993-1 1,5MMD PIN CONTACT</p>	 <p>TE Part # 1-962982-1 2,5MM RECEPTACLE CONTACT SWS</p>

Customers Also Bought

 <p>TE Part #T1329320140-000 H32A-TG-M40</p>	 <p>TE Part #T2071164101-000 H16BP-T4-M DOCKING FRAME_FLOATING</p>	 <p>TE Part #T2071164201-000 H16BP-T4-F DOCKING FRAME_FIXED</p>	 <p>TE Part #900412-2 PC I/O RETENTION LEG ASSY 80P</p>
 <p>TE Part #1SNK705513R0000 ZK2.5-L-N-PE</p>	 <p>TE Part #AEA110N00000201000 623 RECEPTACLE, SPEEDTEC-READY</p>	 <p>TE Part #ASA013N00610235000 623 PLUG</p>	 <p>TE Part #ASA021N00210235000 623 PLUG</p>
 <p>TE Part #T1660103132-000 H10B-SDRH-LB-M32</p>	 <p>TE Part #T2120100223-000 ZGG-10DST,1-6/3-4/5-10</p>		

Documents



Datasheets & Catalog Pages

CRIMPING TERMINALS

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

SDE Crimp Commercial Tool System

English

Instruction Sheets

Instruction Sheet (U.S.)

English