

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2196791052](#)
Status: **Active**
Overview: [Micro-Latch Wire-to-Board Connector System](#)
Description: [Micro-Latch-to-Pigtail Off-the-Shelf \(OTS\) Cable Assembly, 2.00mm Pitch, Tin \(Sn\) Plating, 150.00mm Length, 5 Circuits, Natural](#)

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	219679
Application	Signal, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	Micro-Latch-to-Pigtail
Overview	Micro-Latch Wire-to-Board Connector System
Product Name	Micro-Latch
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	195842860117

Physical

Cable Length	150.00mm
Circuits (Loaded)	5
Color - Resin	Natural
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.587/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.900µm
Plating min - Termination	0.900µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm
Wire Size AWG	22
Wire/Cable Type	UL 10002


Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2196791050-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
D(2022)9120-DC (17
Jan 2023)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[219679 Series](#)

Mates With

Micro-Latch Vertical Header [53253](#) . Micro-Latch Right-Angle Header [53254](#)