

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2204240006](#)  
**Status:** **Active**  
**Overview:** [Squba Sealed Wire-to-Wire Connectors](#)  
**Description:** [Squba Weather Cap for 6 or 3 Circuit Receptacle Housing](#)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 2042200000-AS-000 (PDF)</a>
<a href="#">Product Specification 2042200000-PS-000 (PDF)</a>	<a href="#">Application Specification 2077760000-AS-000 (PDF)</a>
<a href="#">Product Specification 2042200000-TS-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2077760000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Accessories
Series	<a href="#">220424</a>
Component Type	Cap
Overview	<a href="#">Squba Sealed Wire-to-Wire Connectors</a>
Product Name	Squba
Taxonomy	Connector Accessories
UPC	196823073779

**Physical**

Circuits (Loaded)	3, 6
Circuits (maximum)	3, 6
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	0.920/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2042200000-AS-000, 2077760000-AS-000
Product Specification	2042200000-PS-000, 2042200000-TS-000, 2077760000-PS-000
Sales Drawing	2204240000-SD-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained per -  
D(2022)9120-DC (17  
Jan 2023)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[220424](#) Series

**Use With**

Squba Sealed Receptacle Housing [204220](#) ,  
[207782](#)