

## OPTICAL PATCH CABLE AND ADAPTOR

FOPC	END 1	END 2	CABLE LENGTH	FIBERS	CONSTRUCTION
	-01 = MTP Male	-01 = MTP Male	-003 = 3 Meters	-12, -24	-01 = 3 mm Round Jacket
	-02 = MTP Female	-02 = MTP Female	-010 = 10 Meters		
			-100 = 100 Meters (Other lengths available as custom parts)		

  

OVERALL LENGTH = CABLE LENGTH ±5%

**-01-01-XXX-12-01**

**-02-02-XXX-24-01**

**12 FIBER**

  

**24 FIBER**

**SPECIFICATIONS**

**Compliant Specifications:**  
TIA-604-5-D (FOCIS 5)  
TIA-568-C.3  
IEC-61754-7-1

View complete specifications at: [samtec.com?FOPC](http://samtec.com?FOPC)

OPA	PORTS	KEY	FLANGE
	-S = Single	-1 = Opposed	-F = Full
	-D = Double	-2 = Aligned	

  

**-S**

**-D**

**-1**

  

**-2**

**SPECIFICATIONS**

**Compliant Specifications:**  
TIA-604-5-D (FOCIS 5)  
IEC-61754-7

**Recommended Panel Thickness:**  
(1.75 mm) .069"  
(The OPA can be installed with any panel thickness but mounting hardware is needed for any thickness that is not (1.75 mm) .069". Contact the Optics Group at FireFly@samtec.com for questions about panel thickness and mounting hardware.)

View complete specifications at: [samtec.com?OPA](http://samtec.com?OPA)

**Notes:**  
Some lengths, styles and options are non-standard, non-returnable