



26880200

Polyester Ex Okta Box Ex empty

121 x 121 x 75 mm

Polyester Ex Okta Box Ex empty 121 x 121 x 75 mm

[Catalogues](#)
[Operating manuals](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Terminal Mounting](#)

## Technical data

Height	121 mm
Width	121 mm
Depth	75 mm
Material	Polyester
Colour	Graphite black (RAL 9011)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-55 °C
temperature max.	135 °C
Seal material	VMQ-(silicone)
Flammability enclosure (certification)	UL 94 V-0
Toxicity	Halogen free
Surface resistance	<math>10^9</math> Ohm
Surface resistance norm	IEC 60093
Other versions on request	EMV
Special colours on request	No
Approvals	ABS, ATEX, CCOE India, EAC (TR CU), EXPLOLABS, IECEx, INMETRO, ISCVE Ukraine, UL Ex

## Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.491 kg
GTIN	4250157916440

## ETIM classification

ETIM 8	EC002503
--------	----------

ROSE SYSTEMTECHNIK GMBH  
Erbeweg 13-15  
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0  
Fax: +49 571 50 41-6  
Mail: [rose@rose-pw.de](mailto:rose@rose-pw.de)

## Accessories



10016016

Continuity plate for Oktabox Gr. 2