

27010210

Taguan 130 tief, open (with Battery Compartment)



Taguan 130 tief, open (with Battery Compartment)

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[Drawing](#)[3D Data](#)

Technical data

Height	125 mm
Width	80 mm
Depth	46.7 mm
Material	ABS
Colour	ocean blue (RAL 5020)
Ingress protection	IP40
Degree of protection norm	EN 60529
temperature min.	-40 °C
temperature max.	80 °C
Surface resistance	$4 \times 10^{14} \text{ Ohm}$
Other versions on request	EMV

Commercial data

Country of origin	RO
Order unit	1 Piece
Customs tariff number	39269097
Weight	0.123 kg
GTIN	4250157916679










ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

	27010090 Taguan Spare screw set		27010280 Battery holder 4 micro-cells (AAA)
	27010281 Taguan 130 Monoblock holder		27010282 Taguan 130 Clip
	27010285 Taguan Shaft cover RAL 5020		27010287 Taguan Shaft cover infrared
	27010288 Taguan 130 Display screen set		82100001 MEMBRANE KEYPADS FT 130b
	82100002 MEMBRAN KEYPADS FT 130e		