

Order Symbol: AR IPW 108 SCT

Description: Instrument Protection Window

Remarks : Transparent Hinged Screw Cover

Includes: Cover and base with formed in place PUR gasket and hardware and template for mounting frame.



SAMPLE IMAGE

Product Number 8561814

| Dimensions | Length | Width | Height |
|------------|--------|-------|--------|
| Inch | 10.0 | 8.0 | 3.31 |
| mm | 254 | 203.2 | 84.1 |

Materials

Material: Polycarbonate
 Base Color: RAL 7035 - LIGHT GREY
 Cover Color: CLEAR
 Gasket material: Polyurethane

Temperature

Temperature C° (short term): -40° - 120° C"
 Temperature C° (continuous): -40° - 80° C"
 Temperature F° (short term): -40° - 250° F
 Temperature F° (continuous): -40° - 175° F

Ratings

NEMA Class: NEMA 4, 4X, 12, & 13
 Ingress Protection (EN 60529): IP66
 Impact Resistance (EN 62262): IK 09
 Electrical insulation: Fully Insulated
 Halogen free (DIN/VDE 0472, Part 815): YES
 UV Resistance: UL 508
 Flammability Rating: UL94-5VA (f1) / Cover: UL94-V0 (f1)
 Glow Wire Test (IEC 695-2-1) °C: 960 °CC