

Order Symbol: AR IPW 108 W

Description: Instrument Protection Window

Remarks : Gray Cover with Non-locking Wing Handle

Includes: Cover and base with formed in place PUR gasket and hardware and template for mounting frame.



SAMPLE IMAGE

Product Number 8561811

Dimensions	Length	Width	Height
Inch	10.0	8.0	3.31
mm	254.0	203.2	84.1

Materials

Material:	Polycarbonate
Base Color:	RAL 7035 - LIGHT GREY
Cover Color:	RAL 7035 - LIGHT GREY
Gasket material:	Polyurethane

Temperature

Temperature C° (short term):	-40° - 120° C"
Temperature C° (continuous):	-40° - 80° C"
Temperature F° (short term):	-40° - 250° F
Temperature F° (continuous):	-40° - 175° F

Ratings

NEMA Class	NEMA 4, 4X, 12, & 13
Ingress Protection (EN 60529):	IP66
Impact Resistance (EN 62262):	IK 09
Electrical insulation:	Fully Insulated
Halogen free (DIN/VDE 0472, Part 815):	YES
UV Resistance:	UL 508
Flammability Rating:	Base: UL94-5VA (f1)
Glow Wire Test (IEC 695-2-1) °C:	960 °CC