

Order Symbol: AR IPW 1412 W F

Description: Instrument Protection Window

Remarks : Grey Flat Cover with Non-Locking Wing Handle

Includes: Cover and base with formed in place PUR gasket and hardware and template for mounting frame.



SAMPLE IMAGE

Product Number 8561843

Dimensions	Length	Width	Height
Inch	14.0	12.0	2.31
mm	355.6	304.8	58.6

Materials

Material: Polycarbonate
 Base Color: RAL 7035 - LIGHT GREY
 Cover Color: RAL 7035 - LIGHT GREY
 Gasket material: Polyurethane

Temperature

Temperature C° (short term): -40° - 120° C"
 Temperature C° (continuous): -40° - 80° C"
 Temperature F° (short term): -40° - 250° F
 Temperature F° (continuous): -40° - 175° F

Ratings

NEMA Class: NEMA 4, 4X, 12, & 13
 Ingress Protection (EN 60529): IP66
 Impact Resistance (EN 62262): IK 09
 Electrical insulation: Fully Insulated
 Halogen free (DIN/VDE 0472, Part 815): YES
 UV Resistance: UL 508
 Flammability Rating: UL94-5VA (f1)
 Glow Wire Test (IEC 695-2-1) °C: 960 °CC