



#### General Information

Series	ESTX
Description	Flex Suppressor Halogen Free Type
Features	Resonance suppression
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

#### Specifications

Temperature Range	-40/+105°C
Permeability	150 u At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.3 TYP
Surface Resistivity	1 MOhm/sq. TYP

#### Dimensions

L	10000mm NOM
W	9mm NOM
T	0.05mm NOM

#### Packaging Specifications

Tape Thickness	0.03mm
Component Weight	46 g