



02363609

Polyester Enclosure Standard

360 x 360 x 91 mm

Polyester Enclosure Standard 360 x 360 x 91 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

Technical data

Height	360 mm
Width	360 mm
Depth	91 mm
Material	Polyester
Colour	Squirrel Gray (RAL 7000)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	CR-(Chloroprene)
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10 ¹² Ohm
Surface resistance norm	IEC 60093
Special colours on request	Yes
Approvals	Lloyd Register, Maritime Register, UL 508A

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	39269097
Weight	4.11 kg
GTIN	4250157900746

ETIM classification

ETIM 8	EC000058
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011118
Mounting plate for 02.363609



10027001
HINGE EXTERNAL / GREY



10061425
DIN rail 35/7,5 for xx.163609



10062003
Earth rail for 01.163609