



1-Channel Power Unit, digital, 70 W

Item No: T0053298699

1-Channel Power Unit, digital, 70 W

KEY FEATURES

- + Power unit, 1 channel with soldering iron WEP 70 and safety rest PH 70
- + 70 W solder iron with ergonomic handle and providing toolless tip change
- + ESD safe station, iron and heat-resistant silicon cable for safe handling
- + Using ET soldering tips
- + Standby mode and auto setback conserves energy, protects equipment
- + Password-protected to preserve settings
- + Replacement for 4ETH, 4ETK, 4ETO, 4ETS necessary. For WEP 70 4ETHL, 4ETKL, 4EKOL and 4ETSL must be used.
- + Change hot tips out by hand by twisting the plastic knurled nut on the soldering pencil without an additional tool.

TECHNICAL DATA

Width	120.0 mm
Height	98.0 mm
Length	150.0 mm
Dimensions L x W x H	150.0 x 120.0 x 98.0mm
Approximate Heating Time (50-350 °C/120-660 °F)	28 sec
ESD Safe	Yes
Number of Channels	1
Power	85 W
Temperature Accuracy °C	± 5 °C
Temperature Accuracy °F	±5 °C
Temperature Range °C	100 - 450 °C
Temperature Range °F	413 - 842 °F
Temperature Stability °C	±6 °C
Temperature Stability °F	±6 °C
Tip Type	WE
UPC	4003019439973
Voltage	230 V