

## Specification Sheet

Part Number: 151-04017



No drilling or extra hardware required – just secure to steel surface.  
Magnetic mounts are reliable even in debris, dirt, and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without residue.

Magnetic Cable Tie Mount, Grip Tie, 1.02" Dia, Neodymium Magnet/POM/ST, 15lb Pull Force, Blk, 10/Bag

Article Number 151-04017

Type MAGCTM15H

Color Black (BK)

Quantity Per bag

**Product Description**

Magnetic cable tie mounts route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle to the mount with a cable tie and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts. Magnetic cable tie mounts can be paired with HellermannTyton grip ties.

Short Description	Magnetic Cable Tie Mount, Grip Tie, 1.02" Dia, Neodymium Magnet/POM/ST, 15lb Pull Force, Blk, 10/Bag
Global Part Name	MAGCTM15H-NDFEB39/POM/ST-BK
Fixation Method	Magnet
Height H (Imperial)	0.56
Height H (Metric)	14.4
Diameter D (Imperial)	1.02
Diameter D (Metric)	26
Cable Tie Width Max (Imperial)	0.75
Cable Tie Width Max (Metric)	19.1
Material	Neodymium alloy 39M (NDFEB39) Polyacetal (POM) Steel (ST)
Material Shortcut	POM ST NDFEB39
Halogen Free	Yes
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	8505110070

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)