

DEWALT®

DOMINATE DRILLING



DCD800B **20V MAX* XR® BRUSHLESS 1/2" DRILL/DRIVER**

Engineered for professional-grade performance, the 20V MAX* XR® Brushless 1/2" Drill/Driver delivers the power and speed needed for heavy-duty drilling and fastening applications. The high-output brushless motor helps you tackle demanding projects with up to 40% more Unit Watts Out compared to the DEWALT DCD791B using DCB205 battery or DCBP034 DEWALT POWERSTACK™ battery (sold separately)**. Complete a wide range of drilling jobs with this versatile power tool, which outputs up to 2,000 rpm when drilling into construction materials. This lightweight, well-balanced Drill/Driver was built compact to help users comfortably work in tight spaces for extended periods of time. The 3-position, pivoting LED is designed to enhance visibility in dimly lit work areas with its 3 mode settings and up to 70 Lumens of brightness.



GUARANTEED TOUGH.®

DCD800B

20V MAX* XR® BRUSHLESS 1/2" DRILL/DRIVER

HIGH BIT RETENTION
with 1/2" metal ratcheting chuck

**PRO-LEVEL SPEED, CONTROL,
AND PRECISION**
High speed transmission with 2 speed
settings (0-650/0-2,000 rpm)

**COMPLETE
CHALLENGING
PROJECTS**
Up to 40% more UWO
vs the DCD791**

**BRIGHTEN DARK
WORK AREAS**
Adjustable 3-Position, 3 Mode
LED with up to 70 Lumens

**MANAGE &
TRACK TOOLS**
Tool Connect™
System Chip™
Ready (DCE042 sold
separately)



Ensure accuracy when drilling in dark spaces with the versatile LED



Access tight, hard to reach spaces with a 1/2 in. shorter tool head***

* Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

** The DEWALT DCD800B with a DEWALT DCB205 battery (sold separately) provides up to 40% more Unit Watts Out vs. DEWALT DCD791B with a DEWALT DCB205 battery or a DEWALT DCBP034 POWERSTACK™ battery (sold separately).

*** DCD800 is 1/2 in. shorter length compared to the DCD791, tool head only.

SPECIFICATIONS

TOOL WEIGHT	2.82 lb (Tool Only)
TOOL HEIGHT	8.14"
TOOL WIDTH	2.5"
TOOL LENGTH	6.37"
CLUTCH SETTINGS	15
# OF SPEED SETTINGS	2
CHUCK SIZE	1/2"
UNIT WATTS OUT	900 UWO
NO LOAD SPEED	0-650 / 0-2,000 RPM

TOOL WARRANTY

**3
YEAR**
LIMITED
WARRANTY

**1
YEAR**
FREE
SERVICE

**90
DAY**
MONEY BACK
GUARANTEE

KIT OPTIONS

DCD800D2

- (2) DCB203 2.0 Ah battery
- (1) DCB112 Charger
- (1) Kit Bag
- (1) Belt Hook

DCD800P1

- (1) DCB205 5.0 Ah battery
- (1) DCB112 Charger
- (1) Kit Bag
- (1) Belt Hook

DCD800E2

- (2) DCBP034 POWERSTACK™ Compact Battery
- (1) DCB112 Charger
- (1) Kit Bag
- (1) Belt Hook

DCD800D1E1

- (1) DCBP034 POWERSTACK™ Compact Battery
- (1) DCB203 2.0 Ah battery
- (1) DCB112 Charger
- (1) Kit Bag
- (1) Belt Hook