

har-flex Hybrid M str 2+8 SMT PL1 280pcs




Image is for illustration purposes only. Please refer to product description.

Part number	15 72 208 2601 000
Specification	har-flex Hybrid M str 2+8 SMT PL1 280pcs
HARTING eCatalogue	https://b2b.harting.com/15722082601000

Identification

Category	Connectors
Series	har-flex®
Identification	Hybrid
Element	Male connector
Description of the contact	Straight

Version

Termination method	Reflow soldering termination (SMT)
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	10
Number of signal contacts	8
Number of power contacts	2
Pack contents	280 pieces on reel

Technical characteristics

Contact spacing (termination side)	1.27 mm
	2.54 mm
Contact spacing (mating side)	1.27 mm
	2.54 mm
Stacking height	3.25 mm
Rated current	20 A
Rated voltage	50 V AC
	120 V DC



Pushing Performance
 Since 1945

Technical characteristics

Rated voltage	acc. to IEC 60664-1
Rated impulse voltage	1.5 kV
Pollution degree	2
Clearance distance	≥0.4 mm Signal contacts
	≥1.74 mm Power contacts
	≥1.11 mm Signal to power contacts
Creepage distance	≥0.4 mm PCB: Signal contacts
	≥1.74 mm PCB: Power contacts
	≥1.11 mm PCB: Signal to power contacts
	≥0.4 mm Connector: Signal contacts
	≥1.89 mm Connector: Power contacts
	≥1.94 mm Connector: Signal to power contacts
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤25 mΩ
Limiting temperature	-55 ... +125 °C
Performance level	1
Mating cycles	≥500
Test voltage U _{r.m.s.}	0.5 kV Signal
	1.39 kV Signal / Power
	1.39 kV Power / Power
Isolation group	IIIa (175 ≤ CTI < 400)
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D
Coplanarity of contacts	0.12 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side
	Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85366990
GTIN	5713140204805
eCl@ss	27460201 PCB connector (board connector)