

RF Product Information

- RFMTA010504NNRB002 Series for UHF Application at 433 MHz

Application

- UHF433 MHz in Smart Meter, Industrial Data Acquisition System and Door Control System
- Device for external UHF system



ELECTRICAL CHARACTERISTICS


Item	Specification
Frequency Range	433 MHz
Impedance	50 Ohm Nominal
VSWR	3 Max.
Radiation	Omni-directional
Polarization	Linear Vertical
Admotted Power	1W

MATERIAL TABLE


Item	Description
Antenna	Phosphor Bronze

ELECTRICAL


Frequency: 433 MHz




Phi=0.00deg



Phi=90.00deg



Theta=90.00deg



INFORMATION

For more information, please contact with
[Walsin Technology Corporation](http://www.walsin.com)
Tel : 886-3-475-8711
Fax : 886-3-475-5197
E mail : info@passivecomponent.com
Web Site : <http://www.passivecomponent.com>