

SEARCH KEYWORD, PART NUMBER



Part Number: 15363604

SINGLE WIRE SEAL FITS TO 8.5 mm CAVITY



Attributes

Type	Color
SINGLE WIRE SEAL	WHITE
Outer Diameter (mm)	Hardness (Shore)
9	50
Borehole Diameter (mm)	Contains Lubricant (Oil Content)
1.6	Low
Length (mm)	Min. operating temperature
7.8	-40°C
Min Cable Outer Diameter (mm)	Max. operating temperature
2	+140°C
Max Cable Outer Diameter (mm)	
3	