

SEARCH KEYWORD, PART NUMBER



Part Number: 35093138

NO CRIMP / DISK SEAL FITS TO 24.0 mm CAVITY



Attributes

Type	Color
NO CRIMP / DISK SEAL	GRAY
Outer Diameter (mm)	Hardness (Shore)
25.2	50
Borehole Diameter (mm)	Contains Lubricant (Oil Content)
9.1	Low
Length (mm)	Min. operating temperature
10	-40°C
Min Cable Outer Diameter (mm)	Max. operating temperature
9.8	+140°C
Max Cable Outer Diameter (mm)	
11	