

Specification Sheet

Part Number: 170-01161

Self-wrapping woven sleeving made of fiberglass and PET polyester protects against chewing damage.

Provides good protection against abrasion, UV and weathering, vibration and impact.

Quick and easy installation and removal, ideal for retrofitting.

Lightweight material won't add significant weight to the installation.

Resists acids, solvents and micro-organisms for extended performance in industrial environments.



Braided Sleeving, Twist-In Rodent-Repellant Wrap, 13mm Dia. FG/PET, White, 164 ft/rl

Article Number 170-01161

Type Twist-In-RR-13

Color White (WH) Black (BK)

Quantity Per reel

Product Description Twist-In Rodent-Repellent Wrap is a self-closing fiberglass sleeving used to bundle cables and hoses and protect against rodents in infestation-prone areas such as automotive, railways, telecom, underground and waste treatment systems.

Short Description Braided Sleeving, Twist-In Rodent-Repellant Wrap, 13mm Dia. FG/PET, White, 164 ft/rl

| | |
|--------------------------------|-----------------------------------|
| Global Part Name | Twist-In-RR-13-PET/GF-BK/WH |
| Bundle Diameter Min (Imperial) | 0.39 |
| Bundle Diameter Min (Metric) | 10 |
| Bundle Diameter Max (Imperial) | 0.51 |
| Bundle Diameter Max (Metric) | 13 |
| Nominal Diameter (Imperial) | 0.5 |
| Nominal Diameter (Metric) | 12.7 |
| Wall Thickness WT (Metric) | 0.8 |
| Material | Glass Fiber (GF) Polyester (PET) |
| Material Shortcut | PET GF |
| Flammability | FMVSS 302 |
| Halogen Free | No |
| UV Resistant (Yes/No) | No |
| Operating Temperature | -94°F to +257°F (-70°C to +125°C) |
| Reach Compliant (Article 33) | Yes |

| | |
|-----------------------------|--------------|
| ROHS Compliant | Yes |
| Certification/Specification | EN [45545-2] |
| Package Quantity (Imperial) | 164.0 |
| Package Quantity (Metric) | 50 |
| Customs Number | 5808100000 |
| Reel Weight (Imperial) | 4.41 |
| Reel Weight (Metric) | 2.0 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)