

Product Specification PDF

Date	Correct as of 29th Mar 2023
Brand	C.K
Product	T5600
Description	Mighty Scope Inspection Camera
Barcode	5013969248418
Commodity code	8525890000
Country of origin	CN



Features & Benefits	<p>~Wireless inspection camera for the end user needing to inspect, photograph or record video in locations with limited access or visibility. Can be used with C.K Mightyrods/PRO cable routing products. ~Built-in WIFI hotspot</p> <ul style="list-style-type: none"> - Provides high resolution live stream with wireless range up to 50 ft (15m) ~720p HD Streaming - Crisp, clear images with high resolution provides real-time photos and video directly to your smart device ~ Adjustable LED's - Easily access dark, confined spaces with x6 bright white LED's meaning you never lose sight ~ Always up viewing mode - Built in accelerometer detects orientation ensuring live stream remains always up. ~ Digital Zoom Function- View objects closer with greater detail with in-built zoom function ~ Waterproof and dustproof - IP67 rated, 100% protected against dust and dirt ingress, fully submersible to 1m for up to 30 minutes. ~Durable - ABS and anodised aluminium construction for increased durability in use ~Universal - Compatible with both Android and IOS devices using the Free App ~Service - 2 Year Warranty ~ ROHS3 compliant
Applicable Standards	EN 55032:2015+A1 2020 EN 61000-3-2:2019+A1 2021 EN 61000-3-3:2013+A1 2019+A2 2021 EN55035:2017+A11:2020 EN301 489-1 V2,2,3 , EN301 489-17 V3,2,4 EN300 328-1 V2,2,2, EN50665:2017, EN IEC 62311:2020 EN IEC 62368-1-2020+A11 2020 EN IEC 62368-1:2020+A11:2020 Protection against Electric Shock - Class III
Health & Safety	Caution: Bright Light. Do not stare directly into light source.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	-	-
Width mm	-	104mm	-	-
Depth mm	-	50mm	-	-
Height mm	-	185mm	-	-
Weight	206	233	-	-
Packaging Information	Card use	Box	-	-
	Card gms	35	-	-
	Plastic use	0	-	-
	Plastic gms	0	-	-
	Metal use	0	-	-
	Metal gms	0	-	-
	Timber use	0	-	-
	Timber gms	0	-	-