

Product Datasheet

Product code: **E5162.CR.BGS**

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5162 is a high precision cutter belonging to the extra large oval cutter family. This type of geometry provides excellent resistance, while the 5162L head dimensions increase its cutting capacity. The full-flush cutting edge is suitable to perform very clean cuts on small size material. The 5162 is equipped with an ESD Ergo-tek handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Extra Large Oval

Cutting edges: Full-Flush

Cutting capacity: soft wire 0.30-1.60 mm (29-14 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek - Thermoplastic Elastomer + PP compound

Picture:



Dimensions: OAL (A) 130.0 mm – 5.118 inch
 Width 60.0 mm – 2.362 inch
 Height 21.0 mm – 0.827 inch

Head dimensions: Width (C) 16.0 mm – 0.630 inch
 Thickness (D) 6.4 mm – 0.252 inch
 B 14.0 mm – 0.551 inch
 F 0.5 mm – 0.020 inch

