

## Product Datasheet

**Product code:** **MM.SA.6**

**Product type:** Boley tweezers

**Made in:** Italy

**Description:** Type MM Boley tweezers are suitable to applications which require holding a component firmly.

**Tip description:** straight, fine, pointed, strong

**Coating/finishing:** Sandblasted

**Body material:** Anti-Magnetic Anti-Acid Stainless Steel (SA)


**Picture:**




**Tweezer dimensions:**

OAL	125.0 mm – 4.921 inch
Width	11.0 mm – 0.433 inch
Height	11.0 mm – 0.433 inch

**Tip details:**



Dimensions mm



Dimensions inch



**Tip dimensions:**

Tip width	0.50 mm – 0.020 inch
Tip thickness	0.50 mm – 0.020 inch