

Product Datasheet

- Product code:** **ES5160.CR.BGS**
- Product type:** High Precision Cutters
- Made in:** Switzerland
- Head description:** Extra Large, Oval
- Cutting edges:** Semi-Flush
- Cutting capacity:** soft wire 0.40-2.00 mm (26-12 AWG)
- Body material:** High carbon-chromium low alloy steel (100Cr6)
- Body finishing:** Sandblasted
- Handle material:** Ergo-tek Slim - Thermoplastic Elastomer + PP compound
- Picture:**



Dimensions: OAL (A) 125.0 mm – 4.921 inch
 Width 60.0 mm – 2.362 inch
 Height 21.0 mm – 0.827 inch

Head dimensions: Width (C) 16.0 mm – 0.630 inch
 Thickness (D) 6.4 mm – 0.252 inch
 B 14.0 mm – 0.551 inch
 F 0.5 mm – 0.020 inch

