

Product Datasheet

Product code: **ES5162L.CR.BGS**

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5162L is a high precision cutter belonging to the extra large oval cutter family. This type of geometry provides excellent resistance, while the 5162L head dimensions increase its cutting capacity. The full-flush cutting edge is suitable to perform very clean cuts on small size material. The 5162L is equipped with an ESD Ergo-tek slim handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Extra Large Rounded, Oval

Cutting edges: Full-Flush

Cutting capacity: soft wire 0.40-2.50 mm (26-10 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek Slim - Thermoplastic Elastomer + PP compound

Picture:



Dimensions: OAL (A) 127.0 mm – 5.000 inch
 Width 60.0 mm – 2.362 inch
 Height 18.0 mm – 0.709 inch

Head dimensions: Width (C) 16.0 mm – 0.630 inch
 Thickness (D) 6.4 mm – 0.252 inch
 B 13.0 mm – 0.512 inch
 F 0.6 mm – 0.024 inch

