

Product Datasheet

Product code: ES6012.CR.BG

Product type: High Precision Pliers

Made in: Switzerland

Description: The 6012 is a high precision plier belonging to the flat nose plier family. The short jaw length increases the strength of the hold. The serrated surface on the jaw increases its holding capacity. The 6012 is equipped with an ESD Ergo-tek slim handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The jaws are hardened to 45HRC hardness.

Head description: Short, Flat Nose

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek Slim - Thermoplastic Elastomer + PP compound

Picture:



Dimensions: OAL (A) 130.0 mm – 5.118 inch
Width 60.0 mm – 2.362 inch
Height 18.0 mm – 0.709 inch

Head dimensions: Width (C) 10.0 mm – 0.394 inch
Thickness (D) 6.4 mm – 0.252 inch
B 18.0 mm – 0.709 inch
E 1.0 mm – 0.039 inch
F 3.5 mm – 0.138 inch

