

Product Datasheet

Product code: ES5350.CR.BG

Product type: High Precision Cutters

Made in: Switzerland

Description: The 5350 is a high precision cutter belonging to the large tapered cutter family. This type of geometry and head dimensions offer an advantage to support the cut. The semi-flush cutting edge is suitable to perform robust cuts. The 5350 is equipped with an ESD Ergo-tek slim handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharge. The blades are hardened to 67HRC hardness.

Head description: Large, Tapered

Cutting edges: Semi-Flush

Cutting capacity: soft wire 0.30-1.60 mm (29-14 AWG)

Body material: High carbon-chromium low alloy steel (100Cr6)

Body finishing: Sandblasted

Handle material: Ergo-tek Slim - Thermoplastic Elastomer + PP compound

Picture:



Dimensions:

OAL (A)	123.0 mm – 4.843 inch
Width	60.0 mm – 2.362 inch
Height	18.0 mm – 0.709 inch

Head dimensions:

Width (C)	12.0 mm – 0.472 inch
Thickness (D)	6.4 mm – 0.252 inch
B	12.0 mm – 0.472 inch
F	0.2 mm – 0.008 inch

