

Product information

83 10 015

Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 10 015
EAN	4003773014195
Pliers	red powder-coated
Weight	1,415 g
Dimensions	420 x 67 x 24 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Clamping width	60 mm
Capacities for pipes (diameter)	Ø 2 3/8 Inch
Capacities for pipes (diameter)	Ø 60 mm
Capacities for nuts	60 mm
Inner diameter, inches	Ø 1 1/2 Inch

technical change and errors excepted

