

Product information

83 10 030

Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 10 030
EAN	4003773022329
Pliers	red powder-coated
Weight	3,433 g
Dimensions	650 x 96 x 25 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Clamping width	110 mm
Capacities for pipes (diameter)	Ø 4 3/8 Inch
Capacities for pipes (diameter)	Ø 110 mm
Capacities for nuts	105 mm
Inner diameter, inches	Ø 3 Inch

technical change and errors excepted

