

## Product information

# 83 10 040

## Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 10 040
EAN	4003773022336
Pliers	red powder-coated
Weight	4,921 g
Dimensions	750 x 88 x 25 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Clamping width	130 mm
Capacities for pipes (diameter)	Ø 5 1/8 Inch
Capacities for pipes (diameter)	Ø 130 mm
Capacities for nuts	130 mm
Inner diameter, inches	Ø 4 Inch

technical change and errors excepted

